

870 mm (BleedBox)

850 mm (TrimBox)

2270 mm (BleedBox)

2250 mm (TrimBox)

2000 mm (visible area)

BleedBox: minimum 10 mm

Please set bleedbox to 10 mm in your print file. Those 10 mm will be cut away after printing.

TrimBox:

850 x 2250 mm

Margins: minimum 5 mm

No important texts or images should be placed outside margins set inside the TrimBox. If possible, avoid placing important elements where trimming/ folding occurs due to manufacturing tolerances.

Working area:

This part of the print is hidden in the cassette and will not be visible after installation.

Make sure to remove this layout template from your print file!

250 mm (covered area)