

870 mm (BleedBox)

850 mm (TrimBox)

2420 mm (BleedBox)

2400 mm (TrimBox)

2150 mm (visible area)

**BleedBox: minimum 10 mm**

Please set bleedbox to 10 mm in your print file. Those 10 mm will be cut away after printing.

**TrimBox:**

850 x 2400 mm

**Margins: minimum 5 mm**

No important texts or images should be placed outside margins set inside the TrimBox. If possible, avoid placing important elements where trimming / folding occurs due to manufacturing tolerances.

**Working area:**

This part of the print is hidden in the cassette and will not be visible after installation.

**Make sure to remove this layout template from your print file!**

250 mm (covered area)